HSX-650 Medical Heat Sealer



TOUCH SCREEN PRECISION MEDICAL HEAT SEALER FOR REPEATABLE HIGH OUALITY HEAT SEALS AND DETERMINATION OF HEAT SEAL THRESHOLD. PRODUCES SEALS 5 TO 25MM WIDE AND UP TO 650MM LONG.



Benefits:

- Choose heat sealing bar configuration, either single (upper) or dual (upper & lower, meets ASTM F2029)
- Sealing bar can be specified to suit various surface areas or surface finishes
- Accurate and repeatable seals due to precision ground sealing faces and advanced jaw guidance system
- Versatile applications for flexible materials, porous and non-porous films, foils and blister packs
- Low Maintenance 12 months between calibrations

Settings screen for all control parameters



Temperature and pressure calibration screen

Features:

- 5.7" touch screen controller for precise control of temperature, pressure and dwell time
- Memory recipe function for quick and accurate recall of settings
- Precise pressure calibration of standard surface area jaw face
- laws constructed in aluminium and silicon with precision ground faces
- Range of jaw face surfaces including Matched Crimp and Teflon Coating
- Auto cycle feature for greater user convenience and cycle counter



RDM Test Equipment Unit 39 Golds Nurseries Bus. Park Jenkins Drive, ELSENHAM Hertfordshire, CM22 6JX, UK





HSX-650 Medical Heat Sealer



Specification

Temperature

Environment

Models HSX-650 SingleProd - Upper jaw temperature controlled

HSX-650 DualProd - Upper & Lower jaw temperature controlled

Seal Width Up to 650 mm max.

Controller 5.7" Touch Screen TFT LCD 320 x 240 colour display. IP56 rated.

Stores up to 20 sealing recipes. Password protection. Optical pack in place sensors. Auto, touch screen or optional footswitch operation. Range: Ambient to 300° C, Accuracy: +/- 0.5%, Operating Accuracy:

Control +/-2°C. User definable alarm for over/under set level.

Pressure Range: 0 to 100psi (6.8bar, 689Kpa), via electronic pneumatic E/P

regulator. Accuracy +/-1%. User definable alarm for over/under set level. Supply via clean and dry compressed airline or bottled air/

nitrogen at 75 to 115psi

Dwell Time Range: 0.1 to 99.9 sec., Resolution 0.1 sec

Auto Cycle & Delay Time Range: 0.1 to 99.9 sec

Delay Time Auto Cycle incorporates 'Pack-in-place' sensors for automatic cycling

of sealing bars used in manual production environments, and assists

with correct alignment of sample.

Jaw Guidance Advanced jaw guidance system guarantees even closure, resulting in

System consistently high quality seals.

Pre-Heat Cycle User definable variable time interval, electronic processor

controlled.

Cycle Counter Electronic counter for seals completed.

Sealing Jaws Standard flat jaws 25mm x 650mm, constructed in aluminium with

precision ground face. Lower sealing jaw with precision ground

silicone rubber face. (See options below) 5-50C ambient operating temperature,

RH 75% max (non-condensing)

Power 240V AC 50/60 Hz (110V AC available on request)





Options

Separate Control Console

- Sealing jaw dimension/profile as required
- Teflon Coated Tape or Teflon Coated Jaws
- Vacuum and/or gas flushing of packs
- Guillotine cutter
- Integral or separate control console (photos show both versions)
- Validation documentation / service



RDM Test Equipment Unit 39 Golds Nurseries Bus. Park Jenkins Drive, ELSENHAM Hertfordshire, CM22 6JX, UK

> Tel: +44(0)1279 817171 Fax: +44(0)1279 815743 E-mail: sales@rdmtest.com Web: www.rdmtest.com

